



Meet Your Filtration Needs Is Our Goal.

## SS-UE005-8338

UF Membrane for Pharmaceutical, Biological, Food and Dairy Applications

### PRODUCT DESCRIPTION

<b>Membrane Chemistry:</b>	Proprietary semi-permeable polyethersulfone (PES)
<b>Membrane MWCO:</b>	5,000 Daltons
<b>Construction:</b>	Sanitary spiral wound element with net outer wrap Feed spacer: F=31 mil, G=46 mil, H=65 mil, I=80 mil
<b>Options:</b>	Outer wrap: N= Control Bypass without Tail T= Control Bypass with Tail

### SPECIFICATIONS

Model	Active Membrane Area			
	FN/T Spacer (31mil)	GN/T Spacer (46mil)	HN/T Spacer (65mil)	IN/T Spacer (80mil)
	ft <sup>2</sup> (m <sup>2</sup> )	ft <sup>2</sup> (m <sup>2</sup> )	ft <sup>2</sup> (m <sup>2</sup> )	ft <sup>2</sup> (m <sup>2</sup> )
SS-UE005-8338	400 (37.1)	320 (29.7)	250 (23.2)	210 (19.5)

Replacements: KOCH 8338 HFK-328; NADIR DS-UP005-8338  
Specialty feed spacer is available.

### OPERATION SPECIFICATIONS


<b>Typical Operation Pressure:</b>	30-120 psi (2.1-8.3 bar)
<b>Maximum Operation Pressure:</b>	140 psi (9.7 bar)
<b>Operating Temperature Range:</b>	41-122°F (5-50°C)
<b>Cleaning Temperature Range:</b>	105-122°F (40-50°C)
<b>pH-Continuous Operation @25°C</b>	2.0-10.0
<b>pH-CIP @25°C</b>	1.8-11.0

Contact us for specific applications.

### DESIGN PARAMETERS

<b>Feed:</b>	F spacer:100-113 gpm
	G spacer:125-140 gpm
	H spacer:148-164 gpm
	I spacer:172-190 gpm
<b>Design Pressure Drop Per Element:</b>	F spacer:12-15 psi (0.8-1.0bar)
	G spacer:15-20 psi (1.0-1.4bar)
	H & I spacer:15-25 psi (1.0-1.7bar)

### DIMENSIONS



Model	A	B	C
	inches (mm)	inches (mm)	inches (mm)
SS-UE005-8338	38.0 (965)	8.3 (211)	1.138 (28.9)

RisingSun Membrane Technology (Beijing) Co., Ltd. [www.risingsunmem.com](http://www.risingsunmem.com)

Add: Building 2, Shunren Road No.51, Linhe Industrial Zone, Shunyi District, Beijing, China Post Code:101300

Tel:86-10-89496869 Fax:86-10-89496839 Mail: [info@risingsunmem.com](mailto:info@risingsunmem.com)